

Quick Start Guide

USB-C 3.1 SATA SSD/HDD Water-Resistant Enclosure with Built-In Cable for 2.5-Inch Drives

Models: U457-025-G1-WPG (USB 3.1 Gen 1, 5 Gbps),
U457-025-G2-WPB (USB 3.1 Gen 2, 10 Gbps)

Este manual esta disponible en español en la página de Tripp Lite:
tripplite.com/support

Ce manuel est disponible en français sur le site Web de Tripp Lite :
tripplite.com/support

Русскоязычная версия настоящего руководства представлена на веб-сайте компании Tripp Lite по адресу: tripplite.com/support

WARRANTY REGISTRATION

Register your product today and be automatically entered to win an ISOBAR surge protector in our monthly drawing!

tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • tripplite.com/support

Copyright © 2019 Tripp Lite. All rights reserved.

Product Features

- Converts any 2.5 in. internal SATA SSD (solid state drive) or HDD (hard disk drive) into an external hard drive for storing data
- Designed for 2.5 in. SATA drive heights between 7 mm and 9.5 mm
- Supports SATA III (6 Gbps), II (3 Gbps) and I (1.5 Gbps) drives
- Backward compatible with USB 3.0, 2.0 and 1.1 devices
- Water-resistant and dust-tight to comply with IP66 standards
- UASP-compatible for enhanced performance
- Bus-powered plug-and-play operation with no software or external power required

Package Contents

- U457-025-G1-WPG (SuperSpeed USB 3.1 Gen 1, 5 Gbps) or U457-025-G2-WPB (SuperSpeed USB 3.1 Gen 2, 10 Gbps)
- Mini Screwdriver
- Screws (x10)
- Washers (x10)
- Quick Start Guide

System Requirements

- USB 3.1 Gen 1 (5 Gbps) port required to achieve maximum speeds for U457-025-G1-WPG
- USB 3.1 Gen 2 (10 Gbps) port required to achieve maximum speeds for U457-025-G2-WPB
- UASP-enabled host controller required to achieve UASP performance
- 2.5 in. SATA HDD or SSD with maximum height of 9.5 mm

Installation

- 1 Remove the back cover (side with the screw holes) of the SSD/HDD enclosure.
- 2 Connect your 2.5 in. SATA SSD/HDD to the SATA connector.
- 3 Once the SATA SSD/HDD is securely in place, replace the back cover, ensuring the screw holes line up with one another.
- 4 Using the included screwdriver, screws and washers, fasten the 10 screws and washers securely to the enclosure.
Note: In order to comply with IP66 standards, screws need to be properly tightened to the enclosure.
- 5 Connect the built-in USB 3.1 Type-C cable to an available USB port on your computer.

Specifications

Drive Connection	22-Pin SATA Data + Power
USB Connection	USB Type-C (Male)
Maximum Data Transfer Rate	10 Gbps (U457-025-G2-WPB) 5 Gbps (U457-025-G1-WPG)
SSD/HDD Supported	2.5 in. SATA I/II/III HDD/SSD
Operating Temperature	50° to 122°F (10° to 50°C)
Relative Humidity	10% to 80% RH, Non-Condensing
Dimensions	0.94 x 3.7 x 5.8 in. (24 x 94 x 148 mm)

Warranty and Product Registration

1-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of one (1) year from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way. EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

Product Registration

Visit triplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

WARNING

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



1111 W. 35th Street, Chicago, IL 60609 USA • triplite.com/support