

7-Port Industrial-Grade USB 3.2 Gen 2 Hub

Model:
U460-4A3C-IND

USB Type-C® and
USB-C® are registered
trademarks of USB
Implementers Forum.



Purchased product
may differ from image.

Este manual está disponible en español en la página de Eaton:
Tripplite.Eaton.com/support

Ce manuel est disponible en français sur le site Web de Eaton :
Tripplite.Eaton.com/support

Dieses Handbuch ist in deutscher Sprache auf der Eaton-Website verfügbar:
Tripplite.Eaton.com/support

Questo manuale è disponibile in italiano sul sito web di Eaton:
Tripplite.Eaton.com/support

EATON

Powering Business Worldwide

Important Safety Instructions

- Always read the safety instructions carefully
- Keep this Owner's Manual for future reference
- If any of the following situations arise, schedule an appointment to have your equipment inspected by a service technician:
 - o The equipment has been exposed to moisture
 - o The equipment has been dropped and damaged
 - o The equipment shows obvious signs of breakage
 - o The equipment is not functioning properly or is not functioning according to the Owner's Manual instructions

Product Features

- Add four USB-A and three USB-C ports to the USB-C port on your laptop, Ultrabook or computer
- USB 3.2 Gen 2 compliant with data transfer rates up to 10 Gbps
- Backward compatible with previous USB generations
- Rugged all-metal enclosure designed for industrial applications
- USB-C ports support USB cables with locking connectors
- Two power connection options (2-wire terminal block or user-supplied external power supply)
- All device USB ports are BC 1.2-compliant, providing up to 1.5A of fast charging power to mobile devices (when connected to power)
- USB-C device ports support both data and charging
- All ports can be used simultaneously, with each port providing up to 900mA of power
- Overcurrent detection and protection
- ESD protection to +/- 15 kV
- EFT protection +/- 2.5 kV
- Automatic link and speed detection
- Plug-and-play—no software or drivers required

System Requirements

- Compatible with all USB-enabled operating systems

Package Contents

- U460-4A3C-IND
- USB 3.2 Gen 2 (10 Gbps) Type-C Cable, 2 ft. (0.6 m)
- 2-Wire Terminal Block
- Owner's Manual

Optional Accessories:

- U322-Series USB 3.0 A/B Device Cables
- U326-Series USB 3.0 Micro-B Device Cables
- U420-003-G2 USB 3.2 Gen 2 (10 Gbps) Type-C (Male/Male) Cable, 3 ft. / 0.9 m
- U422-003-G2 USB 3.2 Gen 2 (10 Gbps) Type-C to USB 3.0 Type B (Male/Male) Cable, 3 ft. / 0.9 m
- U426-003-G2 USB 3.2 Gen 2 (10 Gbps) Type-C to USB 3.0 Micro-B (Male/Male) Cable, 3 ft.

Powering the Hub

Power Terminal

A 2-wire terminal block is installed on the unit to power the hub via power terminal.

DC-In

To power the hub, connect a user-supplied 12-24V DC power adapter to the unit and a wall outlet.

Note: *The U460-4A3C-IND is compatible with listed limited power source (LPS) power supplies from 12V DC to 24V DC. These power supplies use a 2.5 x 5.5 x 9.5 mm input plug with either a positive tip and negative sleeve, or a negative tip and positive sleeve.*

Operation

1. Using the included USB Type-C cable, connect the USB-C port labeled Host to your laptop, computer or any USB-C device.
2. Using the included terminal block or a user-supplied power adapter, power the unit via the desired powering method. A blue LED will illuminate to indicate the unit is receiving power from the power source.
3. Connect up to four USB devices to the USB-A hub ports.
4. Connect up to three USB devices to the USB-C hub ports.
5. LEDs will illuminate green as each device is connected to indicate it is connected to the hub.

Note: *If USB ports are not properly working, unplug all devices, as well as the power source. After 10 seconds, repeat installation steps.*

Specifications

Input Connector	4x USB 3.0 Type-A (Female) 3x USB Type-C (Female)
Output Connector	USB Type-C (Female)
LEDs	Blue: Power Green: Connection
ESD Protection	+/- 15kV
EFT Protection	+/- 2.5kV
Transmission Speed	Up to 10 Gbps
Power Requirement	12-24V DC Power Supply 2-Pin Terminal (12-24V DC)
Operating Temperature	32 to 122°F / 0 to 50°C
Storage Temperature	14 to 176°F / -10 to 80°C
Operating Humidity	0% to 85% RH, Non-Condensing
Storage Humidity	0% to 95% RH, Non-Condensing
Dimensions, L x W x H	6.5 x 2.5 x 0.8 in. / 165 x 64 x 20 mm
Enclosure Material	Metal

Warranty

3-Year Limited Warranty

We warrant our products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. Our obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. Visit TrippLite.Eaton.com/support/product-returns before sending any equipment back for repair. This warranty does not apply to equipment which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, WE MAKE NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL WE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, we are not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications to this equipment not expressly approved by Eaton could void the user's authority to operate this equipment.

Warranty

WEEE Compliance Information for Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Eaton, they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Eaton has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



Powering Business Worldwide

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2023 Eaton
All Rights Reserved
Publication No. 23-10-043 / 93-3983_RevC
November 2023



933983

Eaton is a registered trademark.

All trademarks are property of their respective owners.