

Quick Start Guide

RJ11/RJ12/RJ45 Crimping Tool with Cable Stripper

Model: T100-001

Package Includes

- T100-001
- Quick Start Guide

Optional Accessories

- N020-Series Cat5e Stranded Conductor Bulk Cable – 1,000 ft.
- N022-01K-GY Cat5e Solid Conductor Bulk Cable, Gray – 1,000 ft.
- N024-01K Cat5e Solid Conductor Plenum-Rated Bulk Cable, Gray – 1,000 ft.
- N028-01K-GY Cat5e Solid Conductor Outdoor-Rated Bulk Cable, Gray – 1,000 ft.
- N030-010 Cat5e RJ45 Plugs for Solid / Stranded Conductor Cable – 10 Pack
- N030-100 Cat5e RJ45 Plugs for Solid / Stranded Conductor Cable – 100 Pack
- N030-100-FL Cat5e RJ45 Plugs for Solid / Stranded Conductor Flat Cable – 100 Pack
- N031-050 Cat5e RJ45 Plugs for Stranded Conductor Cable – 100 Pack
- N222-Series Cat6 Solid Conductor Bulk Cable – 1,000 ft.
- N224-01K-GY Cat6 Solid Conductor Plenum-Rated Bulk Cable, Gray – 1,000 ft.
- N230-100 Cat6 RJ45 Plugs for Solid / Stranded Conductor Cable – 100 Pack

Opening / Closing the Tool

To open the tool handles, simply squeeze them together and release. To lock the handles in place, squeeze them together slightly (one or two clicks only) and release. You can also release the handles by turning the knob in-between the handles counterclockwise.

Cutting Cable

On one side of the tool is a single blade for cutting cable. Insert the cable to the desired length into the slot underneath the blade. Then cut the cable by squeezing the handles together until the cable cleanly separates.

PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate peace of mind.
You could also win an ISOBAR6ULTRA surge protector—a \$100 value!

www.tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support

Copyright © 2015 Tripp Lite. All rights reserved.

Stripping Flat Cable

4-Pin/6-Pin – On the same side of the tool as the double blades, insert the cable in-between the blades until it hits the rectangular stopper. Squeeze the tool's handles to score each side of the cable, then pull off the jacket.

8-Pin – On the same side of the tool as the double blades, insert the cable in-between the blades until the cable comes out just past the cutting blade on the other end. Squeeze the tool's handles to score each side of the cable, then pull off the jacket.

Stripping Round Cable

Insert the cable into the slot located in front of the lower scoring cable. Squeeze the tool's handles and rotate the tool around the cable to score the jacket. Pull off the jacket.

Crimping Connectors

Once jacket has been stripped from the cable, insert the cable wires into an appropriate plug. Follow by inserting the plug into the tool's corresponding 6-Pin or 8-Pin slot, then squeeze the handles to crimp.

Warranty and Product Registration

1-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of one (1) year from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

PRODUCT REGISTRATION

Visit www.tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended. Do not use this equipment in the presence of a flammable anesthetic mixture with air, oxygen or nitrous oxide.



1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support