

Quick Start Guide

USB-C and USB-A to RJ45 Gigabit Ethernet Network Adapter, 10/100/1000 Mbps, Black

Model: U336-000-GB-CA

Este manual está disponible en español en la página de Tripp Lite:
tripplite.com/support

Ce manuel est disponible en français sur le site Web de Tripp Lite :
tripplite.com/support

Русскоязычная версия настоящего руководства представлена на веб-сайте компании Tripp Lite по адресу: tripplite.com/support

Dieses Handbuch ist in deutscher Sprache auf der Tripp Lite-Website verfügbar: tripplite.com/support

WARRANTY REGISTRATION

Register your product today and be automatically entered to win an ISOBAR® surge protector in our monthly drawing!
tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • tripplite.com/support

Copyright © 2021 Tripp Lite. All rights reserved. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum.

Product Features

- Connects the USB port on your computer, laptop or tablet to a wired Ethernet network
- Ensures full 10/100/1000 Mbps (1 Gbps) network speeds
- Compliant with IEEE 802.3, 802.3u, 802.3ab and 802.3az standards
- Supports:
 - o Wake-on-LAN
 - o Full duplex with IEEE 802.3X flow control
 - o Half duplex with back-pressure flow control
 - o IPv4 and IPv6 pack Checksum Offload Engine (COE)
 - o Suspend model and remote wake-up via link change, Magic Packet, Microsoft Wakeup Frame and external wake-up pin
- Compatible with Windows® and macOS® operating systems
- Plug-and-play operation with no external power needed for easy connection
- Fits easily into pocket, backpack, briefcase or laptop bag

System Requirements

- Computer, laptop or other compatible device with USB ports (USB 3.0 required to achieve USB 3.0 speeds)
- Windows or macOS operating system


Optional Accessories

- N201-Series Cat6 Gigabit Snagless Molded UTP Ethernet Cables

Package Contents

- U336-000-GB-CA
- USB-A to USB-C Plug Adapter
- Quick Start Guide

Installation



1. Connect the built-in USB-A cable to the USB-A port on your computer or laptop.
2. If your computer has a USB-C port, connect the included USB-C plug adapter to the USB-A cable, and connect the cable to the USB-C port.
3. Connect the RJ45 port to an Ethernet network with a user-supplied UTP cable.
4. A white LED will indicate when the U336-000-GB-CA is connected to your computer. An orange LED will indicate when an Ethernet network connection is made.

Specifications

Input/Output Connectors	
Input	USB-A (Male) USB-C Adapter (Male)
Output	RJ45 (Female)
Physical	
Dimensions (H x W x D)	7.7 x 0.9 x 0.6 in. / 19.6 x 2.2 x 1.5 cm
Weight	0.5 oz. / 14.6 g
Specifications	
USB	5 Gbps (USB 3.2 Gen 1)
RJ45	10/100/1000 Mbps (1 Gbps)
LEDs	White: Power Orange: Network Activity
Networking	
IEEE Standards Supported	802.3, 802.3ab, 802.3az, 802.3u
Environmental	
Operating Temperature Range	32° to 113°F / 0° to 45°C
Storage Temperature Range	14° to 158°F / -10° to 70°C
Operating Humidity Range	10 to 85% RH, Non-Condensing
Storage Humidity Range	5 to 90% RH, Non-Condensing
Compatibility	
Operating Systems	Windows and macOS
Accessories	
User Manual	English Version
Warranty	
Limited Warranty	3 Years

Warranty and Product Registration

3-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of three (3) years from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, at its sole discretion.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND CONSEQUENTIAL DAMAGES. (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from jurisdiction to jurisdiction.)

WARNING: The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

Product Registration

Visit tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

*No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Warranty and Product Registration

WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite, they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



1111 W. 35th Street, Chicago, IL 60609 USA • triplite.com/support