

### Dual-Port USB Car Charger 4 ft. Charge/Sync Connector, 30W

Model:  
U280-C02-30W-K



Purchased product  
may differ from image.

Este manual está disponible en español en la página de Eaton:  
[Tripplite.Eaton.com/support](https://Tripplite.Eaton.com/support)

Ce manuel est disponible en français sur le site Web de Eaton :  
[Tripplite.Eaton.com/support](https://Tripplite.Eaton.com/support)

Dieses Handbuch ist in deutscher Sprache auf der Eaton-Website verfügbar:  
[Tripplite.Eaton.com/support](https://Tripplite.Eaton.com/support)

Questo manuale è disponibile in italiano sul sito web di Eaton:  
[Tripplite.Eaton.com/support](https://Tripplite.Eaton.com/support)



*Powering Business Worldwide*

## Product Features

- Internal chip allows 100–240 VAC of input
- Features 2 charging ports:
  - USB-A: 12W (5V 2.4A)
  - USB-C PD 3.0: 18W (5V 3A, 9V 2A)
- Prevents overheating, overcharging, overloads and short circuits to protect your devices from damage
- Intelligent LED indicates charging status at a glance
- Travel-sized design takes up little space in your dashboard


## Package Contents

- U280-C02-30W-K 30W Dual-Port USB Car Charger
- USB-C to Lightning Cable, 4 ft.
- Quick Start Guide

## Operation

**Note:** If the Dual-Port Car Charger's over-current, over-temperature or short-circuit protection causes the charger to shut down, disconnect your devices immediately. Please check to ensure your devices are compatible with the Dual-Port Car Charger.

1. Plug the Dual-Port Car Charger into your vehicle's 12V power jack and wait for the LED to turn on.
2. Connect your device(s) to the output port(s) for charging.
3. When your device(s) are fully charged, disconnect them from the Dual-Port Car Charger.



## Specifications

<b>Input/Output</b>	
Input Plug	12V Power Jack
Input	100–240 VAC; 50/60 Hz
Output	USB-A: 12W (5V 2.4A) USB-C PD 3.0: 18W (5V 3A, 9V 2A)
<b>Protection</b>	
Over Current	Yes
Short Circuit	Yes
Over Temperature	Yes
Over Voltage	Yes
<b>Performance</b>	
Ripple and Noise	≤100mV
Turn On Delay Time	<3 s
Rise Time	<20 ms
Efficiency	≥ 87%
<b>Mechanical</b>	
Color	Black
Size	2.6 x 1.3 in. / 6.6 x 3.3 cm
<b>Environmental</b>	
Operating Temperature Range	32° to 86°F (0° to 30°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	30% to 90% RH
Storage Humidity Range	10% to 90% RH
Certification	RoHS, REACH, CE, FCC, WEEE, MFi
Limited Warranty	2 Years

## Warranty and Product Registration

### 1-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of one (1) year from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, at its sole discretion.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND CONSEQUENTIAL DAMAGES. (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from jurisdiction to jurisdiction.)

WARNING: The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Eaton has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.







Eaton  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2023 Eaton  
All Rights Reserved  
Publication No. 23-06-388 /  
93-3D20\_revB  
June 2023

Eaton is a registered  
trademark.

All trademarks are property  
of their respective owners.